

Fiber Handlers

For 900 μm and jacketed cable for UniCam® and OptiSnap® Flat Cleavers

CORNING

Fiber Handlers and Track for UniCam® and OptiSnap® Flat Cleavers.

The double-sided fiber handler works with 900 μm tight-buffered fiber and jacketed cable for UniCam® and OptiSnap® Flat Cleavers.



Part Number: HAN-STANDARD



Part Number: HAN-STANDARD

CORNING

Fiber Handlers

For 900 μ m and jacketed cable for UniCam® and OptiSnap® Flat Cleavers

CORNING

Specifications

General Specifications

Technology	No-Epoxy/No-Polish
Product Type	Connector Tools and Tool Kits

Mechanical Characteristics

Weight	0.016 kg (0.035 lb)
--------	---------------------

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	HAN-STANDARD
Product Description	Double-sided Fiber Handler for Tight-Buffered 900 μ m and jacketed cable for UniCam® and OptiSnap® Flat Cleavers

Shipping Information

Units per Delivery	1/1
Package Contents	Double-sided Fiber Handler for Tight-Buffered 900 μ m and jacketed cable for UniCam® and OptiSnap® Flat Cleavers



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks. Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING