

Ha-VIS eCon 2000



Ethernet Switch  
Ha-VIS eCon 2030-A  
3-port Ethernet Switch for flat mounting onto top-hat mounting rail in control cabinets

|           |       |                     |                        |
|-----------|-------|---------------------|------------------------|
| Unmanaged | IP 30 | PROFINET compatible | EtherNet/IP compatible |
|-----------|-------|---------------------|------------------------|

|                                       |                                                         |
|---------------------------------------|---------------------------------------------------------|
| Number of ports, Copper / Termination | 3x 10/100Base-T(X) / RJ45 (Twisted Pair)                |
| Input voltage / Termination           | 24 V DC / 3-pole, pluggable screw contact (24 V, 0, FE) |
| Permissible range (min./max.)         | 9.6 V ... 36 V DC                                       |
| Input current                         | approx. 100 mA (at 24 V DC)                             |
| Housing material                      | aluminium, anodised                                     |
| Dimensions (W x H x D)                | 46.5 x 105 x 25.5 mm (without connectors)               |
| Weight                                | approx. 0.2 kg                                          |
| Working temperature                   | -10 °C ... +70 °C                                       |
| Approvals                             | UL 508; UL 60 950-1; DNV                                |
| MTBF                                  | 1.020.000 h                                             |

| Identification                                             | Part number    | Drawing | Dimensions in mm |
|------------------------------------------------------------|----------------|---------|------------------|
| Ha-VIS eCon 2030-A<br>Ethernet Switch with<br>3 RJ45 ports | 20 76 103 3000 |         |                  |