

Identification	Part number 180°	0°	270°	90°
HARTING PushPull RJ45 System cable, angled, 4-wire one side pre-assembled, second side open Type A				
Length 1.5 m	09 47 390 0003	09 47 400 0003	09 47 370 0003	09 47 380 0003
Length 3.0 m	09 47 390 0005	09 47 400 0005	09 47 370 0005	09 47 380 0005
Length 5.0 m	09 47 390 0007	09 47 400 0007	09 47 370 0007	09 47 380 0007
Length 10.0 m	09 47 390 0012	09 47 400 0012	09 47 370 0012	09 47 380 0012
Length 20.0 m	09 47 390 0014	09 47 400 0014	09 47 370 0014	09 47 380 0014
HARTING PushPull RJ45 System cable, angled, 4-wire one side pre-assembled, second side open Type B				
Length 1.5 m	09 47 390 0025	09 47 400 0025	09 47 370 0025	09 47 380 0025
Length 3.0 m	09 47 390 0027	09 47 400 0027	09 47 370 0027	09 47 380 0027
Length 5.0 m	09 47 390 0029	09 47 400 0029	09 47 370 0029	09 47 380 0029
Length 10.0 m	09 47 390 0034	09 47 400 0034	09 47 370 0034	09 47 380 0034
Length 20.0 m	09 47 390 0036	09 47 400 0036	09 47 370 0036	09 47 380 0036
HARTING PushPull RJ45 System cable, angled, 4-wire one side pre-assembled, second side open Type C				
Length 1.5 m	09 47 390 0047	09 47 400 0047	09 47 370 0047	09 47 380 0047
Length 3.0 m	09 47 390 0049	09 47 400 0049	09 47 370 0049	09 47 380 0049
Length 5.0 m	09 47 390 0051	09 47 400 0051	09 47 370 0051	09 47 380 0051
Length 10.0 m	09 47 390 0056	09 47 400 0056	09 47 370 0056	09 47 380 0056
Length 20.0 m	09 47 390 0058	09 47 400 0058	09 47 370 0058	09 47 380 0058
HARTING PushPull RJ45 System cable, angled, 4-wire one side pre-assembled, second side open Outdoor				
Length 1.5 m	09 47 390 0069	09 47 400 0069	09 47 370 0069	09 47 380 0069
Length 3.0 m	09 47 390 0071	09 47 400 0071	09 47 370 0071	09 47 380 0071
Length 5.0 m	09 47 390 0073	09 47 400 0073	09 47 370 0073	09 47 380 0073
Length 10.0 m	09 47 390 0078	09 47 400 0078	09 47 370 0078	09 47 380 0078
Length 20.0 m	09 47 390 0080	09 47 400 0080	09 47 370 0080	09 47 380 0080