

LANC 19" Patch Panel Housing

For 24 LANC Modules or 4 Standard Splice Cassettes

CORNING

Corning Cable Systems LANC product family provides an economical solution fulfilling the basic requirements for a cabling solution in Enterprise LAN applications. The LANscape® LANC 19" 1U patch panels provide up to 48 fibre (24 port) capacity for LC duplex connectivity and 24 fibre (12 port) capacity for ST or SC duplex connectivity.

Features and Benefits

Durable steel construction, 1 mm thick

Finished in powder coated, black, RAL 9005

Provides solution for pigtail splicing or direct termination (UniCam®)

Accepts LANC adapter modules which easily snap into position

Holds up to 4 splice cassettes for 48 fibre capacity

Fixed mounting; no moving parts

Easy cover removal for top access by loosening 2 screws; screw removal not required



Specifications

General Specifications

Environment	Indoor
Mounting Type	Rack 19"
Mounting Technology	Flush mount
Access Type	Front access fixed
Lockable	No

Design - Hardware

Housing Material	Metal
Housing Colour	Grey
Height Unit	1U
Number of Ports	24

LANC 19" Patch Panel Housing

For 24 LANC Modules or 4 Standard Splice Cassettes



Mechanical characteristics

Dimensions (HxWxD)	42 mm x 480 mm x 220 mm
Weight	2.0 kg

Ordering Information

Part Number	LANC-01U-G
Product Description	LANC 19" Patch Panel Housing, 1U, grey, for 24 LANC Modules and up to 4 Standard Splice Cassettes

Shipping Information

Packing dimensions (L x W x H)	60 mm x 555 mm x 355 mm
Shipping Weight	2.3 kg
Units per Delivery	10/1



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · www.corning.com/cablesystems/emea

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/emea/trademarks. Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.

