

FutureCom™ Patch Panel 19", 1U, 24 Ports

High-grade steel

CORNING

The FutureCom™ patch panel is universally applicable for all 19-in racks and LAN-cabinets. This allows the free user-specific configuration of building and floor distributors.

The front panel is electrically leading. Integrated grounding points are available at the back. Likewise for grounding 2 latches are available for flat connectors. Particularly to emphasize is the simple and fast installation and clicking of the modules into the patch panel.

Features

- Suitable for all LANscape modules (FO and Copper)
- Robust metal construction, high-grade steel



Specifications

General Specifications

Environment	Indoor
-------------	--------

Design - Hardware

Number of Ports	24
Colour	high-grade steel
Height Unit	1U
Housing material	High-grade steel

Mechanical characteristics

Dimensions (L x W x H)	483 mm x 44 mm x 152 mm
------------------------	-------------------------

Chemical characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
Environmental compatibility	Recyclable

FutureCom™ Patch Panel 19", 1U, 24 Ports

High-grade steel

CORNING

Ordering Information

Part Number	WAXWSV-02400-C001
Product Description	FutureCom™ 19-in Patch Panel, for up to 24 LANscape® fibre optic or FutureCom™ copper modules, with integrated cable strain relief, 1U, high-grade steel
Colour	high-grade steel
Height Unit	1U
Weight	0.725 kg

Shipping Information

Units per Delivery	1/1
--------------------	-----



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · www.corning.com/cablesystems/emea

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/emea/trademarks. Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.