

# FutureCom™ Patch Panel 19", 1U, 24 Ports

Black

CORNING

The FutureCom™ patch panel is universally applicable for all 19-in racks and LAN-cabinets. This allows the free user-specific configuration of building and floor distributors.

The front panel is electrically leading. Integrated grounding points are available at the back. Likewise for grounding 2 latches are available for flat connectors. Particularly to emphasize is the simple and fast installation and clicking of the modules into the patch panel.

## Features

- Suitable for all LANscape modules (FO and Copper)
- Robust metal construction, black



## Specifications

General Specifications	
Environment	Indoor

  

Design - Hardware	
Number of Ports	24
Colour	Black
Height Unit	1U
Housing material	High-grade steel

  

Mechanical characteristics	
Dimensions (L x W x H)	483 mm x 44 mm x 152 mm

  

Chemical characteristics	
RoHS	Free of hazardous substances according to RoHS 2002/95/EG
Environmental compatibility	Recyclable

# FutureCom™ Patch Panel 19", 1U, 24 Ports

Black



## Ordering Information

Part Number	WAXWSV-02408-C001
Product Description	FutureCom™ Patch Panel 19-in, for up to 24 LANscape® or FutureCom™ modules, integrated strain relief, 1U, 24 Ports, black
Colour	black
Height Unit	1U
Weight	0.722 kg

## Shipping Information

Units per Delivery	1/1
--------------------	-----



Corning Cable Systems GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, Germany

TEL: 00800-2676-4641 (00800-CORNING1) · FAX: +49-30-5303-2335 · [www.corning.com/cablesystems/emea](http://www.corning.com/cablesystems/emea)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/emea/trademarks](http://www.corning.com/cablesystems/emea/trademarks). Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.