

CAT-Z J-Hook with Rod/Wire Clip – CAT124Z34 (181240)



- Threaded rod attachment with attached CADDY® CABLECAT J-hook
- Supports low voltage cables



| | |
|-----------------------------|---------------------------|
| Part Number | CAT124Z34 |
| Article Number | 181240 |
| Material | Steel |
| Finish | Pre-galvanized |
| Diameter | 3/4" 19 mm |
| Flange Thickness | 1/8" – 3/8" 3 – 9.5 mm |
| Rod Size | 1/4" M6 |
| Wire Size | #12 – #8 4.8 – 5 mm |
| Standard Packaging Quantity | 40 pc |
| UPC | 78285633310 |
| UNSPSC | 39131709 |
| EAN-13 | 8711893115154 |
| ETIM | EC000754 |
| Approvals | cULus |

cULus is a registered certification mark of UL LLC.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

