

CADDY® CAT HP J-Hook with Hammer-On Flange Clip – CAT16HP24SM (181098)



- Requires only a hammer to install
- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Rounded edges on J-Hooks provide proper bend radius support for high performance data cables
- Cost effective alternative to expensive cable tray
- Meets ISO®/IECSM 14763-2, TIASM 568-C and TIASM 569-C



Part Number	CAT16HP24SM
Article Number	181098
Material	Steel
Finish	Pre-galvanized CADDY® ARMOUR
Area	1.07 in ² 690 mm ²
Cable Capacity, Cat 5e	20
Cable Capacity, Cat 6	15
Cable Capacity, Cat 6A	10
Diameter (Ø)	1 " 25 mm
Flange Thickness (FT)	1/8 " – 1/4 " 3 – 6 mm
Static Load (F)	60 lb 270 N
Standard Packaging Quantity	50 pc
UPC	78285680121
UNSPSC	39131709
Approvals	cULus®

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIASM 569-C.9.7.

Cable capacity is calculated based on a 70% fill rate.

cULus is a registered certification mark of UL LLC. IEC is a registered service mark of Independent Electrical Contractors, Inc. ISO is a registered trademark of International Organization for Standardization. TIA is a registered service mark of the Telecommunications Industry Association.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

