


CADDY® CAT HP J-Hook with Multi-Function Clip – CAT16HP4Z34 (181217)



- Quick attachment to threaded rod or wire
- Provides optimal support for high-performance data cable, including CAT6, CAT6A, CAT7 and fibre optics
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Rounded edges on J-hooks provide smoother cable pull
- Cost effective alternative to expensive cable tray
- Meets EN 50174-2, ISO®/IEC® 18010, TIA-568-C and TIA-569-C



Part Number	CAT16HP4Z34
Article Number	181217
Material	Steel
Finish	Pre-galvanized CADDY® ARMOUR
Area	1.07 in ² 690 mm ²
Cable Capacity, Cat 5e	20
Cable Capacity, Cat 6	15
Cable Capacity, Cat 6A	10
Diameter (Ø)	1" 25 mm
Rod Size (RS)	1/4" M4 M8
Wire Size	#12
A	1' – 5' 1.2 – 1.5 m
Static Load (F)	60 lb 270 N
Standard Packaging Quantity	50 pc
UPC	78285671653
UNSPSC	39131709
Approvals	cULus

cULus is a registered certification mark of UL LLC. ISO is a registered trademark of International Organization for Standardization.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

