

CAT-H J-Hook with Flange Clip – CAT21912SM (181570)



- Hammer-on beam clamp with attached CADDY® CABLECAT J-hook
- Supports low voltage cables



Part Number	CAT21912SM
Article Number	181570
Material	Steel
Finish	Pre-galvanized
Diameter	1 5/16" 33 mm
Flange Thickness	9/16" – 3/4" 14 – 19 mm
Standard Packaging Quantity	40 pc
UPC	78285630237
UNSPSC	39131709
EAN-13	8711893118964
ETIM	EC000754
Approvals	cULus

cULus is a registered certification mark of UL LLC.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

