

CADDY® CAT HP J-Hook with Hammer-On Flange Clip, Swivel – CAT64HP24 (181216)



- Requires only a hammer to install
- Swivels to support various directional runs of cable
- Provides optimal support for high-performance data cable, including CAT6, CAT6A, CAT7 and fibre optics
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Rounded edges on J-hooks provide smoother cable pull
- Cost effective alternative to expensive cable tray
- Meets EN 50174-2, ISO®/IEC® 18010, TIA-568-C and TIA-569-C



Part Number	CAT64HP24
Article Number	181216
Material	Steel
Finish	Pre-galvanized CADDY® ARMOUR
Area	15.48 in ² 9,987 mm ²
Cable Capacity, Cat 5e	330
Cable Capacity, Cat 6	220
Cable Capacity, Cat 6A	140
Diameter (Ø)	4" 100 mm
Flange Thickness (FT)	1/8" – 1/4" 3 – 6 mm
A	1' – 5' 1.2 – 1.5 m
Static Load (F)	60 lb 270 N
Standard Packaging Quantity	25 pc
UPC	78285671669
UNSPSC	39131709
Approvals	cULus

cULus is a registered certification mark of UL LLC. ISO is a registered trademark of International Organization for Standardization.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2013 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

