

EN
Instructions for use
LB1-BW12-D
LB1-BW12-L

Security Systems



Cabinet Loudspeaker

LB1-BW12-L 12W Bi-directional cabinet (white)
LB1-BW12-D 12W Bi-directional cabinet (black)

Type number overview:

Technical performance data acc. to IEC 60268-5

	LB1-BW12-D/LB1-BW12-L
Max. power	18 W
Rated power (PHC)	12 W
Sound pressure level	97/86 dB
at rated power/1W (at 1kHz,1m)	
Effective frequency range	140 Hz to 20 kHz
(-10 dB)	
Opening angle (at 1kHz	
/4kHz, -6dB)	
Horizontal	270/162
Vertical	
Rated voltage	100V
Rated impedance	833 Ohm
Size of speaker	5.25" (2 x)
Magnet weight	2.8 oz
Ambient temperature range	-25 to 55 C
Safety	EN 60065
Connection	4-pole push- n termina block
Dimension(HxWxD)	240x238x152
Colour	
Cabinet/front	Matches RAL 9010/RAL 7044 (L)
Cabinet/front	Matches RAL 9004/RAL 9004 (-D)
Weight	1.5kg



