LBC 3941/11 Sound Projector

www.boschsecurity.com





- ► Excellent speech and music reproduction
- Very wide opening angle
- ▶ Modern unobtrusive styling
- ▶ Simple power setting
- ► Splash waterproof

The LBC 3941/11 is a 6 W cost-effective sound projector. It features a very wide opening angle and unobtrusive styling. Water and dust protection to IP 65 make it suitable for indoor and outdoor use.

Functions

The sound projector features a very wide opening angle (90 degrees) which means fewer units are required to cover a given area. Its wide frequency range also results in better speech and music reproduction, while the directivity ensures that the sound is accurately projected to where it is needed most.

The LBC 3941/11 sound projector is finished in an attractive white color, and its unobtrusive appearance complements today's interior lighting. The color and styling of the front grille matches an existing Bosch ceiling loudspeaker (LBC 3951/11).

Certifications and approvals

All Bosch loudspeakers are designed to withstand operating at their rated power for 100 hours in accordance with IEC 268-5 Power Handling Capacity (PHC) standards. Bosch has also developed the Simulated Acoustical Feedback Exposure (SAFE) test to demonstrate that they can withstand two times

their rated power for short durations. This ensures extra reliability under extreme conditions, leading to higher customer satisfaction, longer operating life, and much less chance of failure or performance deterioration.

The enclosures are made from high-impact self-extinguishing ABS (according to class UL 94 VO).


Safety	acc. to EN 60065	
Water and dust protection	acc. to EN 60529, IP 65	
Self-Extinguishing	acc. to UL 94 VO	

Region	Certification
Europe	CE


Installation/configuration notes

The sound projector is supplied with a steel mounting bracket painted in white. The bracket has three 10 mm holes, which can be used to easily mount the projector to walls and ceilings. The direction of the projector can be adjusted by means of two screws covered with white plastic covers. The unit is supplied with a 2 m color-coded five-core cable, with each color connected to a different primary tap on the matching


transformer. This makes it easy to select full-power, half-power, quarter-power and eighth-power radiation without opening the unit during installation.




Circuit diagram



Dimensions in mm (in)



Frequency response



Polar diagram (measured with pink noise)

	125 Hz	250 Hz	500 Hz	1 kHz	2 kHz	4 kHz	8 kHz
SPL 1.1	82	84	83	88	92	88	88
SPL max.	90	92	91	96	10 0	96	96
Q-factor	1.2	1.2	1.6	2.9	5.1	8.5	18
Efficien cy	0.17	0.26	0.16	0.2 8	0.3 9	0.0 9	0.0 4
H. angle	360	360	360	18 0	12 0	90	60
V. angle	360	360	360	18 0	12 0	90	60

Acoustical performance specified per octave

Technical specifications

Electrical*

Maximum power	9 W
Rated power	6/3/1.5/0.75W
Sound pressure level at 6 W / 1 W (1 kHz, 1 m)	96 dB / 88 dB (SPL)
Sound pressure level at 6 W / 1 W (2 kHz, 1 m)	100 dB / 92 dB (SPL)
Opening angle at 1 kHz / 4 kHz (-6 dB)	180°/90°
Effective frequency range (-10 dB)	130 Hz to 18 kHz
Rated voltage	100 V

3 | LBC 3941/11 Sound Projector

Rated impedance	1667 ohm
Connection	2 m 5-wire cable

^{*} Technical performance data acc. to IEC 60268-5

Mechanical

Dimensions (D x L)	165 x 200 mm (6.50 x 7.87 in)
Speaker diameter	100 mm (4 in)
Weight	1.5 kg (3.3 lb)
Color	White (RAL 9010)
Magnet weight	101 g (3.57 oz)

Environmental

Operating temperature	-25 °C to +55 °C (-13 °F to +131 °F)
Storage temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative humidity	<95%

Ordering information

LBC 3941/11 Sound Projector

6 W, white ABS Order number LBC3941/11

Represented by:

Americas:

Americas: Bosch Security Systems, Inc. 12000 Portland Avenue South Burnsville MN 55337, USA Phone: +1-800-392-3497 Fax: +1-800-955-6831 audiosupport@us.bosch.com www.boschsecurity.com

Europe, Middle East, Africa:

Bosch Security Systems B.V. P.O. Box 80002 5617 BA Eindhoven, The Netherlands Phone: + 31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security Systems 11 Bishan Street 21 Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com www.boschsecurity.asia

China:

China:
Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398 www.boschsecurity.com.cn

America Latina:

America Latina:
Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
al.securitysystems@bosch.com
www.boschsecurity.com