

Overview



WayPoint-30A



WayPoint-30A Outdoor Power Supply provides 24VAC and/or 28VAC distributed via one or two output(s) for powering CCTV Cameras, heaters and other video accessories.

Specifications

Input:

- Input: 115VAC, 50/60Hz, 3.5 amp or 230VAC, 50/60Hz, 2.0 amp.

Output:

- Output options:
 - a. 24VAC @ 12.5 amp max.
 - b. 28VAC @ 10 amp max.
 - c. Both 24VAC and 28VAC not to exceed 10 amp max.
- Output fuses rated @ 15A 32V.

Electrical:

- Operating Ambient Temperature: -20° C to 50° C.
- 153.55 BTU/Hr.:
- System AC input VA requirement:
 - 115VAC: 402.5VA.
 - 230VAC: 460VA.

Features:

- Individual power output LEDs.
- Spare fuses included.

Mechanical:

- NEMA 4/4X, IP66-11 Rated enclosure for outdoor use.
- Lightweight molded fiberglass reinforced polyester enclosure is corrosion resistant and does not contain halogens.
- Lockable stainless steel latches.
- Integral flanges simplify wall or pole mounting.
- Enclosure Dimensions (H x W x D approx.): 13.31" (338.074 mm) x 11.31" (287.274 mm) x 5.59" (141.986 mm).
- Product weight (approx.): 15.45 lbs. (7.01 kg).
- Shipping weight (approx.): 16.75 lbs. (7.6 kg).

Agency Approvals



European Conformity

PMK1 Pole Mount Kit (order separately)



PMK1

PMK1 pole mount kit is designed to simplify installation of outdoor units.

- Accommodates 2"- 8"(diameter) poles.
- Kit includes:
 - Two (2) powder coated steel mount brackets.
 - Four (4) stainless steel bolts.
 - Four (4) stainless steel lock washers.
 - Two (2) wormgear quick release straps.

Enclosure Dimensions (H x W x D):

13.31" (338.074 mm) x 11.31" (287.274 mm) x 5.59" (141.986 mm)

