



# GEIST

# EPP



Product Number G2100 Basic Power 4way 1UH UK



for illustrative purposes only

**Description:** Geist's basic power range provides no-frills, 100% guaranteed power distribution in the rack. This horizontal four way, switched unit provides a simple and reliable way to power servers. Supplied with a 3m x 1.5mm<sup>2</sup> PVC lead to BS1363 plug as standard, this basic PDU is an excellent, cost-effective unit from a great value range.

## Key Features:

### Electrical

Socket type & quantity - output  
Switch  
Power-on indicator  
Plug - power input  
Lead - type & length  
Type  
Voltage  
Amps  
Frequency

4 x BS1363 (UK)  
Green neon with protective flip-up cover  
Via switch  
BS1363 13Amp  
3 metre x 1.5mm<sup>2</sup> PVC  
Single phase  
230V  
13A  
50/60Hz

### Environmental

Operating temperatures

0 - 45° C

### Physical:

Size (Dimensions H x W x D)  
Construction  
Colour - RAL  
Texture  
Unit weight  
Packaged Unit (H x W x D)

44mm x 483mm x 50mm  
Powder Coated Rolled Steel  
Black - RAL 9005  
Fine  
1.5kg  
60mm x 523mm x 117mm

## Switch & socket:



## Physical Cont:

Fixing

Provided

Warranty

Lifetime

Certifications

CE, RoHS, IEC60950-1

## Technical Drawing:

All measurements shown in millimetres

