



## Description:

Geist's basic power range provides no-frills, 100% guaranteed power distribution in the rack. This vertical ten way RH-angled, switched unit provides a simple and reliable way to power servers. Supplied with a 3metre x 2.5mm<sup>2</sup> H07 RNF lead to IEC60309 16Amp plug as standard, this basic PDU is an excellent, cost-effective unit from a great value range.

## Key Features:

### Electrical

Socket type & quantity - output  
Switch  
Plug - power input  
Lead - type & length  
Type  
Voltage  
Amps  
Frequency

10 x RH-angled BS1363 (UK) sockets  
Green neon with protective flip-up cover  
IEC60309 16Amp 230V 1P+N+E  
3 metre x 2.5mm<sup>2</sup> H07 RNF  
Single phase  
230V  
16A  
50/60Hz

### Environmental

Operating temperatures

0 - 45° C

### Physical:

Size (Dimensions H x W x D)  
Construction  
Colour - RAL  
Texture  
Unit weight  
Packaged Unit (H x W x D)

978mm x 54mm x 50mm  
Powder Coated Rolled Steel  
Black - RAL 9005  
Fine  
3.9kg  
1000mm x 170mm x 85mm

## Socket Detail:



images for illustrative purposes only

## Physical Cont:

### Fixing

Toolless mounting hardware - 933mm. L-shaped brackets x 2, dimensions: 35mm long, 25mm slot each end

### Warranty

Lifetime

### Certifications

CE, RoHS, IEC60950-1

## Technical Drawing:

All measurements shown in millimetres

