

Description:

Geist's basic power range provides no-frills, 100% guaranteed power distribution in the rack. This vertical twelve way RH-angled, unswitched unit provides a simple and reliable way to power servers. Supplied with a 3 metre x 4.0mm² H07 RNF lead to IEC60309 32Amp plug as standard, this basic PDU is an excellent, cost-effective unit from a great value range.

Key Features:

Electrical

Socket type & quantity - output
Switch
Plug - power input
Lead - type & length
Type
Voltage
Amps
Frequency

12 x RH-angled BS1363 (UK) sockets
None
IEC60309 32Amp 230V 1P+N+E
3 metre x 4.0mm² H07 RNF
Single phase
230V
32A
50/60Hz

Environmental

Operating temperatures

0 - 45° C

Physical:

Size (Dimensions H x W x D)
Construction
Colour - RAL
Texture
Unit weight
Packaged Unit (H x W x D)

978mm x 54mm x 50mm
Powder Coated Rolled Steel
Black - RAL 9005
Fine
4.1kg
1000mm x 170mm x 85mm

Socket Detail:



images for illustrative purposes only

Physical Cont:

Fixing

Toolless mounting hardware - 933mm. L-shaped brackets x 2, dimensions: 35mm long, 25mm slot each end

Warranty

Lifetime

Certifications

CE, RoHS, IEC60950-1

Technical Drawing:

All measurements shown in millimetres

