



GEIST



Product Number G2178 Basic Power C13 16way 1UH 13Amp



for illustrative purposes only

Description: Geist's basic power range provides no-frills, 100% guaranteed power distribution in the rack. This horizontal sixteen way C13, unswitched unit provides a simple and reliable way to power servers. Supplied with a 3m x 1.5mm² PVC lead to BS1363 13Amp plug as standard, this basic PDU is an excellent, cost-effective unit from a great value range.

Key Features:

Electrical

Socket type & quantity - output
Switch
Power-on indicator
Plug - power input
Lead - type & length
Type
Voltage
Amps
Frequency

16 x IEC60320 C13 sockets
None
None
BS1363 13Amp
3 metre x 1.5mm² PVC
Single phase
230V
13A
50/60Hz

Environmental

Operating temperatures

0 - 45° C

Physical:

Size (Dimensions H x W x D)
Construction
Colour - RAL
Texture
Unit weight
Packaged Unit (H x W x D)

44mm x 483mm x 100mm
Powder Coated Rolled Steel
Black - RAL 9005
Fine
1.9kg
65mm x 510mm x 310mm

Socket detail:



Physical Cont:

Fixing

Provided

Warranty

Lifetime

Certifications

CE, RoHS, IEC60950-1

Technical Drawing:

All measurements shown in millimetres

