


1061 (0.009 in. Wall, 300 V)



Product Description

PVC Stranded and solid conductor CSA Type T II SR-PVC

Applications

Internal wiring of electrical and electronic equipment.

Specifications

- CONDUCTOR: Tinned copper
- INSULATION: Polyvinyl Chloride (PVC) (semi-rigid)
- STANDARDS: UL recognized AWM Style 1061 per UL 758. Passes VW-1 vertical flame test. CSA AWM I A/B
- TEMPERATURE: -10°C to 80°C
- VOLTAGE: 300 V

All part numbers require color code designation. If conductor coating differs from standard part number add identifier after stranding (i.e., UL 1061 16/26 prebond light blue with white stripe = 1061-16/26P-L69). Diameters and weights may vary among manufacturers.

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Product Data Sheet | Anixter Catalog Page



Part No.	Conductor AWG	Stranding No. x AWG	Conductor Nom. Dia.	Wire O.D.	Approx. Wt. Ib./1,000 ft.
1061-28/7-XX	28	7x36	0.015	0.035	1.1
1061-26/1-XX	26	Solid	0.016	0.036	1.3
1061-26/7-XX	26	7x34	0.019	0.039	1.5
1061-24/1-XX	24	Solid	0.020	0.041	1.9
1061-24/7-XX	24	7x32	0.024	0.044	2.2
1061-22/1-XX	22	Solid	0.025	0.046	2.7
1061-22/7-XX	22	7x30	0.030	0.051	3.3
1061-20/1-XX	20	Solid	0.032	0.052	3.9
1061-20/10-XX	20	10x30	0.037	0.058	4.1
1061-18/1-XX	18	Solid	0.040	0.061	5.9
1061-18/16-XX	18	16x30	0.048	0.068	6.1
1061-16/1-XX	16	Solid	0.051	0.071	9.1
1061-16/26-XX	16	26x30	0.060	0.078	9.4

Insulation Color Code Chart

0 111
0black
1brown
2red
3orange
4yellow
5green
6blue
7violet/purple
8gray
9white
Ppink
Ttan
Ddark (i.e. D6=dark blue)

L.....light (i.e. L6=light blue)

For white with black stripe - 90
For green with yellow stripe - 54
For white with a black and red stripe - 902
For white and black twisted conductor - 9/0
For white, black and red twisted conductors - 9/0/2

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.