

Technical Specification

Islatrol RM Series Active Tracking Filter / SPD

RM-115-10RM



The **RM-115-10RM** is a 19", rackmount, "Active Tracking®" filter and surge protective device with digital display monitor. Suited for protecting up to twelve 120V, 15A devices. It is ideal for network systems or any applications that requires surge protection and multiple outlets.

Features

LED Indicators	Green LED On - Surge circuit OK
	Green LED On - Ground (earth) OK
	Green LED On - Power On
Digital Display Monitor	Voltage, Amps, Watts, VA, Hz, PF, Kwh, and Clock
Input Power	SJT 14/3 Power Cord (15 ft) with 5-15P Plug
Output Receptacles (Front)	(2) NEMA 5-15R Receptacle
Output Receptacles (Back)	(10) NEMA 5-15R Receptacles
Thermal Protection	Thermal Protected MOVs
	Combo Switch/ Circuit Breaker

Specifications

Electrical Rating	120V, 15A
Peak Surge Current	20kA/mode, 40kA/phase
EMI/RFI Filtering	40dB Max
Suppressed Voltage Rating	400V
Response Time	<5ns
Dimensions	1.75H x 19W x 3.8D (1U)
Weight	5 lbs
Safety Agency Approvals	UL 1449 Recognized