



# exacqVision **ELX-Series**

## Hybrid Server ELX-SR Analog and IP Cameras

### exacqVision ELX-SR


*Compact, Powerful Hybrid NVR Appliance*

*Complete Solution: Operate Server Software, Client and Web Service*

### Key Features & Benefits:

- **Up to 40 Cameras Per Server** — Seamlessly integrate your existing analog and IP cameras from leading camera manufacturers. Includes 8 or 16 analog inputs and up to 16 IP cameras with exacqVision Start and up to 24 IP cameras with exacqVision Professional.
- **High Reliability** — Store up to 8 TB storage per server using rugged continuous duty enterprise class drives for maximum lifespan.
- **All-in-One Solution** — The ELX features an video recording, web/mobile client hosting and local live video display all from the same unit.
- **Unlimited Scalability** — Pre-loaded with exacqVision professional or exacqVision start that easily licenses additional IP cameras up to server's camera, data rate and storage limits. Add unlimited additional servers for greater capacity or dispersed geographic location. Upgrade to enterprise license to easily manage multiple servers.
- **3-Year Hardware Warranty, 3-Year Software Subscription Agreement** — Receive quarterly software updates for all the latest advancements as they are released along with access to technical support. IP camera licenses never expire.
- **Cost-Effective, Compact Chassis** — Professional, compact chassis with optional rackmount kit (1.5U). Stack units for high camera counts.
- **Local, Remote, Web, Mobile User Interfaces** — Access live and recorded video on multiple client PCs with free Windows, Mac or Linux client application. exacqVision web server application pre-installed on server to access video through web browser or free exacqVision iOS and Android apps.



Camera, Alarm & Audio Settings	
IP Camera Inputs	Up to 16 (exacqVision Start) or 24 (exacqVision Pro)
Analog Inputs	8/16
Analog Compression Format	H.264/MJPEG
Analog Frame Rate (NTSC)	240/480
Analog Frame Rate (PAL)	200/400
Serial Connections	2
Alarm Inputs	4 TTL
Alarm Outputs	2 TTL, 1 Relay
Audio Inputs	4
Audio Outputs	0
BNC Video Outputs	1 spot
Storage & Memory	
RAM	2 GB
Drive Bays	2
Storage Maximum (Internal)	8 TB
Features	
NIC	2x1Gb
USB2 Ports	6 x USB 2.0 (2 front, 4 rear)
Monitor Output	1 DVI-I
Processor	Intel i3
Keyboard & Mouse	Included
DVD/CD RW	Included
Watchdog Timer	Included
Server Operating System	Linux Ubuntu 10.04 (kernel 3.0) installed on 4 GB flash drive
VMS Software Included	exacqVision Start (standard), exacqVision Professional or Enterprise (optional)
Compatible Client Operating Systems	Windows 32-bit, 64-bit Mac OS X Linux Ubuntu
Regulatory	CE (Class A), FCC (Class A), UL-Listed
Warranty	3 years parts & labor, 3 years SSA 
Size	
Dimensions (l x w x h)	16.5" x 17" x 2.5" in 42 x 43.2 x 6.4 cm
Weight	12.5 – 14.5 lbs. 5.7 – 6.6 kg
Requirements	
Operating Temperature	40° – 95°F (4.5° – 35°C)
Input Voltage	120/240 VAC auto-sensing
Power Consumption	90W maximum

Specifications subject to change. Visit [www.exacq.com](http://www.exacq.com) for the most current product specifications.

All part numbers can be found in the product catalog at:  
<https://exacq.com/catalog/>



**Exacq Technologies USA**  
11955 Exit Five Parkway  
Fishers, IN 46037 USA

**Exacq Technologies Europe**  
Business & Technology Centre  
Bessemer Drive  
Stevenage, Herts SG1 2DX UK

+1.317.845.5710 USA  
+5255.56080817 Mexico  
+44.1438.310163 UK  
+44.1438.310163 Europe  
+852.8120.9275 Hong Kong

**exacq**<sup>®</sup>  
Technologies  
[www.exacq.com](http://www.exacq.com) 04-13