

QuickPort® 2-Port Surface Mount Housing

APPLICATION

The compact surface mount housing accepts two QuickPort snap-in connector modules. The housing supports voice/data applications in open office, retrofit or other surface mount environments. It includes an ID window, mounting screws and adhesive, and is available in four colors.



SPECIFICATION

The surface mount housing shall be small and low profile to accept two field-configurable QuickPort modules. Base and snap-on cover shall include knockouts for rear, bottom, or side cable entry. Base shall also include cable anchor points. Mounting methods shall include screws, pressure sensitive adhesive, and magnet. Cover shall include an identification window, which also hides a user-provided #6 x 1/2" security screw. Construction shall be of high impact fire retardant plastic rated UL 94V-0. Housing shall be cULus listed and compliant with ANSI/TIA-568-C.

WARRANTY INFORMATION

Visit www.leviton.com/warranty.

COUNTRY OF ORIGIN

United States of America

FEATURES

- User-provided cover screw can be installed for additional security
- Low profile and small overall footprint
- Compatible with all individual QuickPort modules
- Housing base functions as a punchdown platform stabilizing connector modules during termination
- Connector module can be pre-terminated prior to snapping into housing port
- Comes in four colors: white, ivory, grey, and black
- One port shutter included to close off unused ports

DESIGN CONSIDERATIONS

- Choose either screws or adhesive for mounting
- Bottom, side, or rear cable entry options (rear cable entry recommended to help meet cable bend radius standards)
- Accepts magnet (PN: 41030-SMJ) for mounting on steel surfaces
- Allows several port identification methods, including colored modules, designation labels and custom silkscreening
- Allows the use of different colored connectors for different applications to ID ports, 13 TIA-606 compatible connector colors available. Leviton's pre-printed Port Designation Labels are also compatible (PN 41080-L*B)

STANDARDS COMPLIANCE


Meets or exceeds all applicable standards. cULus listed; complies with NEC Article 800 and ANSI/TIA-568-C.

PHYSICAL SPECIFICATIONS

- Dimensions: See page 2
- Materials: High-impact, fire-retardant plastic rated UL 94V-0
- Capacity: Two snap-in QuickPort connector modules
- Mounting: Screws (included) or pressure sensitive adhesive (included), magnet (sold separately)

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



41089-2xP

PART NUMBERS

Description	Part No.
2-Port Surface Mount Housing - White	41089-2WP
2-Port Surface Mount Housing - Ivory	41089-2IP
2-Port Surface Mount Housing - Grey	41089-2GP
2-Port Surface Mount Housing - Black	41089-2EP



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +91.80.4322.5678
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com