

Opt-X Ultra® Fiber Rack-Mount Enclosures

APPLICATION

The Opt-X Ultra Rack Mount Enclosure allows for inter-connect or cross-connect between backbone cable and active equipment while utilizing minimum rack space in frame or cabinet setting. The Enclosure feature set and design allows for installer's ease in field termination of connectors, splicing, or pre-terminated Plug-n-Play solution. It is primarily used in high density fiber application such as data centers, equipment rooms, central offices, etc.



SPECIFICATION

Enclosure with sliding tray shall be available in 1RU, 2RU and 4RU versions that accommodate termination and splicing of fiber. Adapter bulkhead shall accept a variety of modular adapter plates and Plug-n-Play MTP modules/cassettes. Fiber cable management routing and protection shall include patch cord bend radius bracket at entry/exit points, adjustable and stackable cable management rings for tight buffer fiber, cable strain relief kit for incoming backbone fiber, and adjustable saddles for patch cords. Enclosure design shall feature removable transparent polycarbonate doors and covers to ease fiber installation. Enclosure shall be constructed of 16-gauge steel with a powder coat black finish and be mountable in either a 19" or 23" rack or cabinet frame. Locking door feature shall be available as an option. Country of origin shall be the United States of America.

FEATURES

- Stylish and innovative design for today's most advanced networks and settings
- Sliding tray removes completely from enclosure to facilitate field terminations and splicing
- Sliding tray glides forward and backward providing accessibility to front and rear bulkhead after installation
- 17" depth for high density fiber termination and/or splicing
- Removable transparent hinged doors and slide away covers allow easy access during install and visibility of interior after install
- Patch cord bend radius guides minimize macro bending
- Stackable and adjustable fiber rings simplify cable routing and organization
- Saddles pivot for improved patch cord routing and organization
- Removable rubber grommets protect cable and minimize dust build-up
- Multiple mounting bracket positions for 19" or 23" rack and cabinet installation (23" 1RU mounting bracket sold separately)
- Constructed of durable polycarbonate plastic and 16 gauge steel, powder-coated black
- Retrofit Sliding Tray, sold separately, allows for higher density applications using Opt-X Evolve MTP Cassettes

DESIGN CONSIDERATIONS

- Enclosures are sold empty (unloaded)
- Buy components separately, or pre-configure enclosure to your requirements (see second page) or visit www.leviton.com/configurator
- Arrange enclosures to allow future growth
- 19" or 23" rack mount option
- Enclosures protrude 4.5" from mounting ears to align with Leviton's Versi-Duct® Cable Management System
- Specify adapter plate and MTP module selection and capacity (see second page)
- Specify splice tray selection and capacity (see second page)
- Enclosures are capable of storing up to 3 meters of 900 micron tight buffered fiber per adapter
- Door lock option available on front, rear, or both doors
- Enclosure includes an accessory kit consisting of cable ties, mounting screws, ID label, and spiral wrap (for cable protection)

STANDARDS COMPLIANCE

Meets or exceeds all TIA/EIA-568-C.3 requirements.

PHYSICAL SPECIFICATIONS

Capacities and Dimensions: See Page 2


Materials: Constructed of 16 gauge steel, powder coated black. Plastic parts made using self-extinguishing ABS and polycarbonate materials rated UL 94V-2. Grommet material made of Santoprene®, a thermoplastic rubber elastomer.

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, Typical specs, or Dimensional Line Art. (.DXF, .DWG, or .TXT), visit www.leviton.com.



5R1UH-S03 5R2UH-S06 5R4UH-S12

DENSITY			
Rack Unit	Fiber (LC)	Adapter plate / MTP Cassette	Splice Tray
1RU	72	Up to 3	Up to 3 trays
2RU	144	Up to 6	Up to 6 trays
4RU	288	Up to 12	Up to 12 trays

DENSITY USING RETRO-FIT SLIDING TRAY		
Rack Unit	Fiber (LC)	Adapter plate / MTP Cassette (Opt-X Evolve)
1RU	96	Up to 8
2RU	192	Up to 16

Make-to-Order! Opt-X® Ultra Rack-Mount Enclosure Options

ENCLOSURE STYLE	ADAPTER PLATES OR MTP CASSETTE SELECTION	NUMBER OF ADAPTER PLATES	FIBER TYPE	ADAPTER TYPE & PIGTAIL SELECTION	SPLICE TRAY STYLE	NO. OF SPLICE TRAYS	SECURITY OPTIONS	MOUNTING EAR POSITION
<ul style="list-style-type: none"> • 1U Opt-X • 2U Opt-X • 4U Opt-X 	<ul style="list-style-type: none"> • 6 fibers (SC, ST) • 8 fibers (SC, ST) • 12 fibers (LC, SC, ST only) • 16 fibers (LC only) • 24 fibers (LC only) • MTP-12 fibers (LC, SC, ST) • MTP-24 fibers (LC only) 	<ul style="list-style-type: none"> • 1-12 	<ul style="list-style-type: none"> • OM1 • OM2 • OM3 • OM4 • OS2 	<ul style="list-style-type: none"> • LC • LC + pigtail • SC • SC/APC • SC + pigtail • SC/APC + pigtail • ST • ST + pigtail 	<ul style="list-style-type: none"> • Heatshrink, foam holders, up to 12 fibers (molded tray) • Heatshrink, plastic holders, up to 12 fibers (molded tray) • Bare fusion, plastic holders, up to 12 fibers (metal tray) • Heatshrink, plastic holders, up to 24 fibers (molded tray) 	<ul style="list-style-type: none"> • 1-12 • None 	<ul style="list-style-type: none"> • Locking front door • Locking rear door • Both doors • None 	<ul style="list-style-type: none"> • 19" or 23"

For assistance customizing your enclosures, please visit leviton.com/configurator or call Tech Support at 800.824.3005.

NOTE: Unloaded basic part numbers are listed below.

PART NUMBERS - ENCLOSURES & DOORS	
Description	Part No.
1RU Enclosure, empty, with sliding tray	5R1UH-S03
2RU Enclosure, empty, with sliding tray	5R2UH-S06
4RU Enclosure, empty, with sliding tray	5R4UH-S12

Accessory kit consists of cable ties, mounting screws, ID label, and spiral wrap (for cable protection).

PART NUMBERS - ACCESSORIES	
Description	Part No.
Retrofit Sliding Tray, 1U (for use with Opt-X Evolve Cassettes)	5R1UR-TRY
Retrofit Sliding Tray, 2U (for use with Opt-X Evolve Cassettes)	5R2UR-TRY
Universal Opt-X Clamp Kit (for enclosure mounting)	5RCMP-KIT
Universal Opt-X Clamp Kit (for rack post mounting)	5RCMR-KIT
Fiber ¼ Cable Management Ring Kit	5R100-14R*
Grounding Kit	DPGRD-KIT
1RU Enclosure 23" Rack Mounting Bracket	5R1RU-023
1RU Replacement Door	5D000-1UN
2RU Replacement Door	5D000-2UN
4RU Replacement Door	5D000-4UN
1RU Replacement Door w/lock	5D000-1UL
2RU Replacement Door w/lock	5D000-2UL
4RU Replacement Door w/lock	5D000-4UL
Replacement Covers	5C000-RPL

* Not for use in Retrofit Sliding Trays



Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416 tel 1-800-824-3005 tel +1-425-486-2222 appeng@leviton.com www.leviton.com	Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com	Canada T +1.514.954.1840 E pcservice@leviton.com	Caribbean T +1.954.593.1896 E info@caribbean@leviton.com	China T +852.2774.9876 E infochina@leviton.com	Colombia T +57.1.743.6045 E infocolombia@leviton.com
	Europe T +33.6.8869.1380 E infoeurope@leviton.com	India / SAARC T +91.80.4322.5678 E infoindia@leviton.com	Mexico T +52.55.5082.1040 E lsamarketing@leviton.com	Middle East & Africa T +971.4.886.4722 E lmeinfo@leviton.com	South Korea T +82.2.3273.9963 E infokorea@leviton.com