



L6CLICK
Double Click-on Hanger for 1-1/4 in coaxial cable

Dimensions

Nominal Size	1-1/4 in
Compatible Diameter, maximum	40.132 mm 1.580 in
Compatible Diameter, minimum	38.100 mm 1.500 in
Height	51.00 mm 2.01 in
Length	133.00 mm 5.24 in
Width	70.00 mm 2.76 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Package Quantity	10

Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Mounting	3/8 in (M10) drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency

Packed Dimensions

Height	37.7 cm 14.8 in
Length	15.0 cm 5.9 in
Shipping Weight	1.34 kg 2.95 lb
Width	13.9 cm 5.5 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system