

**Broadband Solutions**

760142018 | BOS-CH-03-019

Headend Chassis

Electrical Specifications

Input Current, maximum	8.0 A
Input Voltage	24 Vdc

Mechanical Specifications

Communications Port Interface	10/100 Base-T RJ45
Management Interface	HTTP SNMP agent
Power Supply Dual-Slots Available, quantity	2
Receiver Card Slots Available, quantity	20

General Specifications

Brand	BOS™
Note	Requires power supply
Rack Type	EIA 19 in
Rack Units	3
Warranty	One year

Dimensions

Depth	385.32 mm 15.17 in
Height	132.08 mm 5.20 in
Net Weight	4.99 kg 11.00 lb
Width	482.60 mm 19.00 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system