

Enterprise Solutions

760145052 | PDU-1U-9xC13-OUT-3M-IEC309-EMEA

Horizontal Power Distribution Strip, 230V, 16A, No Surge Protection, No Circuit Breaker, 1U x 19 in x C13 out - 3M IEC309 Plug

Dimensions

Cable Length	3.0 m 9.8 ft
Depth	45.0 mm 1.8 in
Height	41.0 mm 1.6 in
Width	482.6 mm 19.0 in

Electrical Specifications

Current	16.00 A
Overcurrent Protection	No protection
Circuit Breaker	No
On/Off Switch	No
Plug Standard	IEC 309
Power Frequency	50/60 Hz
Power Rating, maximum	3.68 kW
Receptacle Standard	IEC Type C-13
Surge Indicator	No
Surge Protection	No
Voltage	230 V

Environmental Specifications

Safety Standard	CE
-----------------	----

General Specifications

Product Type	Horizontal power strip, 19 in, mounted
Color	Black
Finish	Powder-coated, textured
Includes	Two mounting brackets
Ordering Note	Available in Europe, the Middle East, and Africa
Package, quantity	1
Receptacle, quantity	9

Mechanical Specifications

Material Type	Steel
---------------	-------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications



760145052 | PDU-1U-9xC13-OUT-3MHEC309-EMEA

