

**Enterprise Solutions**

760145078 | PDU-1U-12xC13-OUT-3M-UK-EMEA

**Horizontal Power Distribution Strip, 250V, 13A, No Surge Protection, No Circuit Breaker, 1U x 19 in 12 x C13 out - 3M UK Plug**

## Dimensions

Cable Length	3.0 m   9.8 ft
Depth	45.0 mm   1.8 in
Height	41.0 mm   1.6 in
Width	482.6 mm   19.0 in

## Electrical Specifications

Current	13.00 A
Overcurrent Protection	No protection
Circuit Breaker	No
On/Off Switch	No
Plug Standard	BS1363A (UK)
Power Frequency	50/60 Hz
Power Rating, maximum	3.25 kW
Receptacle Standard	IEC Type C-13
Surge Indicator	No
Surge Protection	No
Voltage	250 V

## Environmental Specifications

Safety Standard	CE
-----------------	----

## General Specifications

Product Type	Horizontal power strip, 19 in, mounted
Color	Black
Finish	Powder-coated, textured
Includes	Two mounting brackets
Ordering Note	Available in Europe, the Middle East, and Africa
Package, quantity	1
Receptacle, quantity	12

## Mechanical Specifications

Material Type	Steel
---------------	-------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications



760145078 | PDU-1U-12xC13-OUT-3MUK-EMEA

