




O2DP8 3.6 - 16mm auto iris varifocal lens



Features:

- Dual-codec (H.264 & MJPEG)
- Progressive scan megapixel (1080p)
- Multi-profile streaming (up to 5 streams of different resolutions, frame rates and codec selections)
- Digital PTZ, video crop
- Analog video output (CVBS)
- Built-in microphone
- PoE IEEE802.3af
- 2-way audio communication
- Built-in true day/night operation
- 3-axis lens mount
- Robust design & convenient installation
- Micro SD card slot (card not included)
- ONVIF support*
- 2 year warranty



Camera Specifications

Image Sensor	Progressive scan 1/2.9" CMOS, 2.0M pixels
Full Resolution	1920 x 1080 pixels (UXGA)
Minimum Illumination (50IRE)	0.12 lux / F1.4 (IR on - 0 lux)
Number of IR LEDs	18
IR LED Wavelength	850nm
IR Range	49' (depending on scene reflection)
S/N Ratio	42db
White Balance	AWB
DSS	Supported
Day/Night	Supported (TDN, IR LED)

Video Specifications

Compression Method	Simultaneous dual-codec (H.264 / MJPEG)
Resolution	1920x1080p @ 30FPS / 1280x720 @ 30FPS
Multi-Profile Streaming	5 simultaneous video profiles
Intelligent Bit-Rate Control	CBR, VBR, HBR
PTZ	Digital PTZ & video crop
Image Setting	Text overlay, privacy mask, de-interlace filter
Motion Detection	3 regions

Audio Specifications

Mono Upstream	32Kbps G.726 ADPCM - LINE-in / MIC-in
Mono Downstream	128Kbps 16-bit Linear PCM - LINE-out (1Vpk)
Stereo	Stereo support

Network Specifications

Network Protocol	IPv4 / v6, TCP, UDP, IGMP, ICMP, ICMPv6, ARP, RARP, PPPoE, RTCP, RTP, RTSP, SDP, HTTP, HTTPS, SMTP, FTP, DHCP, UPnP, SNMP, NTP, DNS, DynDNS, SOCKS
Speco DDNS	Supported (free of charge)
Security	User ID & Password protection, IP address filtering, - HTTPS encryption, digest authentication, user access log, 802.1x support

User Access

8 concurrent users on D1 resolution
Depending on resolution, number of users may vary

*visit www.specotech.com/onvif.html for latest ONVIF support

iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is registered to Google.

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

External Terminal Specifications

LAN	10 / 100 BaseT LAN
Analog Output	1 channel D1 CVBS output of the encoding video
Alarm Input / Output	1 sensor input & 1 relay output
Other	Two Stereo Jack / RS-232 Debug / 12VDC in

System Integration Specifications

Standard PoE (IEEE802.3af)	Supported
Analytics	Motion detection & audio detection
Alarm Triggers	Analytics & sensor input
Alarm Events	Video file upload (FTP), still image (email), relay output

Client Software

Speco NVR	64 ch (free of charge)
-----------	------------------------

Operating Environment

Operating Temperature/	
Humidity	32° F – 113° F / 8% – 80% RH
Power Supply	PoE, 12VDC (power supply not included)
Power Consumption	500mA
Dimensions	5.11" (W) x 3.62" (H)
Weight	1 lb.
Housing	PC / ABS, Ivory
Approvals	FCC, CE, MIC, RoHS
Included in Package	IP camera, CD (user's guide, software), screws
iPhone® / Android™ App	Speco OnSIP

Optional Accessories



DFM
Tile Ceiling
Flush Mount



CVCWMTIND
Indoor
Wall Mount



IPPOEINJ1295
12.95W
PoE Injector



PSW5
12VDC
Power Supply



Rev. 6/28/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com