

VL66 2.8-12mm auto iris varifocal lens, black metal housing
VL66W 2.8-12mm auto iris varifocal lens, white metal housing

Features

- 1/3" Sony Super-HAD™ II CCD
- 650 TV lines of resolution
- Extreme weather resistant design is perfect for indoor or outdoor use (IP67)
- 90' IR range (depending on scene selection), with CDS control for great pictures in low light conditions
- Color by day, BW by night - always get the best possible picture
- Mounting bracket included for wall, ceiling or pedestal use
- Weather resistant operation
- IP67 compliant
- Removable and adjustable sunshield
- 5 year warranty

Specifications

Image Sensor	1/3" Sony Super-HAD™ II CCD
Resolution.....	650 TV lines
Minimum Illumination.....	0 lux with IR on, .092 lux IR off
Total Pixels	976 (H) x 494 (V)
Number of IR LEDs	18
IR LED Wavelength.....	850nm
IR Range	60' – 90' (depending on scene reflection)
Iris.....	Auto
Electronic Shutter Speed.....	1/60 sec. – 1/100,000 sec.
Video S/N Ratio.....	More than 52dB
Gamma.....	0.45 typ.
Video Signal Output.....	1.0Vp-p / 75 Ohms
Scanning System.....	2:1 interlace
Synchronization	Internal
Backlight Compensation.....	Yes
AGC.....	Yes
Operating Temperature/	
Humidity.....	- 4° F – 122° F / 20% – 90% RH
Storage Temperature	- 13° F – 158° F
Power Consumption	LED off: 120mA (12V), 90mA (24V) LED on: 280mA (12V), 220mA (24V)
Power Supply	12VDC / 24VDC dual voltage operation (12VDC power supply included)
Housing	Metal
Dimensions.....	7.5" (L) x 2.87" (W) x 2.48" (Dia.)
Weight	15 oz.
Included in Package	Mounting bracket



Optional Accessory



PSW4
24VAC
Power Supply

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 2/22/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com