

## Rack Mounted Horizontal Transition Trays For Patchcords and Jumpers

- Transition trays offer top and bottom field adjustable horizontal cable management support.
- Bend radius is 1 1/2" (38mm).
- Available for 19" (482mm) and 23" (584mm) racks.
- Material: Aluminum
- Finish\_\_\_: Flat Black Powder Coat (FB) or Silver Powder Coat (SL)

| Catalog Number                                             | Depth  |       | Width |       | Weight |        |
|------------------------------------------------------------|--------|-------|-------|-------|--------|--------|
|                                                            | In.    | (mm)  | In.   | (mm)  | Lbs.   | (kg)   |
| <b>Top Transition Tray - 1 1/2" (38mm) High</b>            |        |       |       |       |        |        |
| ✓ SB81319TT3__                                             | 3 1/2" | (89)  | 19"   | (482) | 3.0    | (1.36) |
| SB81319TT6__                                               | 6"     | (152) | 19"   | (482) | 4.0    | (1.81) |
| SB81323TT3__                                               | 3 1/2" | (89)  | 23"   | (584) | 4.0    | (1.81) |
| SB81323TT6__                                               | 6"     | (152) | 23"   | (584) | 5.0    | (2.27) |
| <b>Upper Transition Tray</b>                               |        |       |       |       |        |        |
| ✓ SB81319UT3__                                             | 3 1/2" | (92)  | 19"   | (482) | 3.0    | (1.36) |
| SB81319UT6__                                               | 6"     | (152) | 19"   | (482) | 4.0    | (1.81) |
| SB81323UT3__                                               | 3 1/2" | (92)  | 23"   | (584) | 4.0    | (1.81) |
| SB81323UT6__                                               | 6"     | (152) | 23"   | (584) | 5.0    | (2.27) |
| <b>Lower Transition Tray</b>                               |        |       |       |       |        |        |
| SB81319LT3__                                               | 3 1/2" | (92)  | 19"   | (482) | 4.0    | (1.81) |
| SB81319LT6__                                               | 6"     | (152) | 19"   | (482) | 5.0    | (2.27) |
| SB81323LT3__                                               | 3 1/2" | (92)  | 23"   | (584) | 5.0    | (2.27) |
| SB81323LT6__                                               | 6"     | (152) | 23"   | (584) | 6.0    | (2.72) |
| <b>Lower Transition Tray - Double - 3 1/2" (89mm) High</b> |        |       |       |       |        |        |
| SB81319LTD3__                                              | 3 1/2" | (92)  | 19"   | (482) | 4.0    | (1.81) |
| SB81319LTD6__                                              | 6"     | (152) | 19"   | (482) | 5.0    | (2.27) |
| SB81323LTD3__                                              | 3 1/2" | (92)  | 23"   | (584) | 5.0    | (2.27) |
| SB81323LTD6__                                              | 6"     | (152) | 23"   | (584) | 6.0    | (2.72) |
| <b>Transition Tray - 1 7/8" (47mm) High</b>                |        |       |       |       |        |        |
| SB813TP3__                                                 | 3 1/4" | (82)  | 15.8" | (401) | 2.0    | (0.91) |
| SB813TP6__                                                 | 5 3/4" | (146) | 15.8" | (401) | 4.0    | (1.81) |

✓ FB is a popular item

