



1Gb CAT6-LAN - CATEGORY 6 SOLID-STATE BUILDING ENTRANCE PROTECTOR

ORDERING INFORMATION

ITW Linx Part Number	Description
CAT6-LAN	Protects high-performance 4-pair CAT 6 Outside Plant Cables as well as CAT 6 UTP cables for LAN/Data applications (16V). Using 110 punchdown In/Out.

* Questions about ordering? Please contact us at **1-800-336-LINX** / Contact an authorized distributor for pricing * (MOQ: 12)

TECHNICAL SPECIFICATIONS

PRODUCT SPECIFICATIONS:

Agency Approval	UL Primary 497 and Isolated Loop (497B)
Grounding Requirements	See Technical Reference page 83-84 for additional grounding tips.
Recommended Grounding Impedance	<0.5 Ohm
Width	4.25"
Height	4.25"
Depth	1.5"
Weight	0.42 lbs
Product Warranty	Lifetime
Connected Equipment Warranty	Up to \$50,000

SIGNAL LINE SURGE PROTECTION: (LAN)

Signal Perfect Circuitry	Yes
Fused	Yes
Performance Rating	Cat 6
Clamping Level	16V
Response Time	1-5 Nanoseconds
Capacitance	<5pF
Wires Protected	4-pairs
Termination Type	110 Punchdown

Features:

- UL listed for Primary (497) and Isolated Loop (497B) applications
- Exceeds TIA/EIA Standards 568 and 758 for CAT 5e performance
- Solid-state protection for fastest response
- Use between buildings in a campus environment as a building entrance protector or in hostile industrial applications as an isolated loop protector
- **Expandable System Protection** - SurgeGate Modules can be attached to one another to expand system protection as your system grows
- **Lifetime Product Warranty** - This surge protector shall be free of any defects in design, materials, or workmanship, or ITW Linx will repair or replace the defective product
- **\$50,000 Connected Equipment**

For up-to-date warranty information, please visit our web site at www.itwlinx.com.



Signal Perfect™



SURGE GATE
SERIES
CAT6 MODULAR
PROTECTOR

