

Canvas Buckets

Aerial-Basket Oval Bucket with 15 Interior Pockets

Additional Features:

- No. 6 canvas.
- Black molded polypropylene bottom.
- Two nylon 66 polymer hooks (Cat. No. 5144H) included with Cat. No. 5144.

| Cat. No. | Length | Width | Height | Pockets | Extra Features | Weight (lbs.) |
|----------|-----------------|----------------|-----------------|-------------------|-------------------------------|---------------|
| 5144 | 14" (356 mm) | 7" (177 mm) | 10" (254 mm) | 15 inside pockets | two hooks (Cat. No. 5144H) | 2.01 |
| 5144B | 14" (356 mm) | 7" (177 mm) | 10" (254 mm) | 15 inside pockets | | 1.5 |



5144

Hard Body Oval Buckets

- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite (Cat. No. 5144BHB14OS).
- Black molded polypropylene bottom with drain holes.



5144BHB



5144BHB14OS



5144BHHB



NEW!

Kick Stand
on back of
Cat. No. 5144BHB

| Cat. No. | Pockets | Handle | Color | Length | Height | Width | Weight (lbs) |
|-------------|---------|--------|--------|--------------|--------------|-------------|--------------|
| 5144BHB | 14 | No | orange | 14" (356 mm) | 10" (254 mm) | 7" (178 mm) | 2 |
| 5144BHHB | 14 | Yes | orange | 14" (356 mm) | 10" (254 mm) | 7" (178 mm) | 2 |
| 5144BHB14OS | 29 | Yes | black | 14" (356 mm) | 10" (254 mm) | 7" (178 mm) | 3 |

- Cat. No. 5144H hooks sold separately.

Hard Body Oval Bucket with Knife Sheath

- Includes leather skinning knife sheath and 14 other interior pockets.
- Orange, non-conductive plastic exterior maintains bucket shape.
- Fabric constructed of rugged denier polyester to resist wear and tear on the jobsite.
- Black molded polypropylene bottom with drain holes.
- Cat. No. 5144H hooks sold separately.

Knife Sheath
inside of
Cat. No. 5144HBS



5144HBS

| Cat. No. | Interior Pockets | Handle | Color | Length | Height | Width | Weight (lbs) |
|----------|------------------|--------|--------|--------------|--------------|-------------|--------------|
| 5144HBS | 15 | Yes | orange | 14" (356 mm) | 10" (254 mm) | 7" (178 mm) | 2 |

All dimensions are in inches and (millimeters).

