

MILESTONE HUSKY SERIES

System Spec - M10 (1 bay – fixed configuration)

Feature	Item	Description
System	Housing	Die casting chassis
	Dimension	200(w)x 200(D) x45(H) mm
	CPU+ Chipset	Intel Atom D2550+NM10
	Memory	4GB DDR3 SO-DIMM on board
Storage	HDD	1 x 2.5" SATA HDD bay (Internal) 1 TB
System I/O	Rear I/O	2 x GbE, RJ45
		4x USB
		1 x DVI 1x HDMI
Power	input	12V DC input
Adapter	60W	100~240V
Environment		Operation Temp: 0~40°C
		Storage Temp: -20°C~ 70°C
OS Support		Linux
Certificate		CE, FCC, UL



MILESTONE HUSKY M10

*Supports up to 8 cameras