

# 50 ohm Coax



## Application

For use with computer and electronic equipment. 50 ohm coaxial cables are available in a variety of styles. These include the following types.

Anixter Number	Nominal Imp (ohms)	Description	Conductor AWG/Type	Dielectric/Jacket Type	% Shield Coverage	Nominal O/D	Nominal Capacitance pF/m
B8214	50	RG8/U B-8214	11 (7 x 19)BC	FPE/PVC	97	10.24	85.3
307-011-058C	50	RG58C/U Black	20 (19 x 32)TC	PE/PVC	95	5.0	101
B8219	50	RG58A/U B-8219	20 (19 x 32)TC	CPE/PVC	95	5.0	93.5
B9907	50	B-9907 Grey	20 (19 x 32)TC	CPE/PVC	93 + 100	4.7	83.3
A7BA-1002	50	URM 76	19 BC	PE/PVC	90	5.0	100
A7BA-1072	50	URM 67	12 BC	PE/PVC	90	10.3	100
B8216	50	RG174/U B-8216	26 (7 x 34)CCS	PE/PVC	90	2.79	101
307-011-214	50	RG214 PVC	(7 x 0.76) SCCX2	PE/PVC	95 98	11.0	100