

# Connectors for Coaxial Cables

Anixter supply a range of plugs, jacks and adaptors for their coaxial cables.



Anixter Number	Description
BNC-C-RG59	BNC straight crimp plug for RG59 (turned body, die-cast nut)
BNC-F-F	BNC straight female - female adaptor
BNC-C-INLINE	BNC straight crimp jack for RG59
BNC-C-RIGHTANGLE	BNC right angle crimp jack for RG59
BNC-T-PIECE	BNC T piece F-M-F adaptor
BNC-GOALPOST	BNC goalpost adaptor
BNC-C-CT100	BNC straight crimp plug for CT100 cable
BNC-C-CT125	BNC straight crimp plug for CT125 cable
BNC-C-CT125RBS	BNC straight crimp plug for CT125RBS cable
BNC-C-CT167	BNC straight crimp plug for CT167 cable
BNC-C-MINI-W	BNC straight crimp plug for Mini RG59 white cable
BNC-C-MINI-B	BNC straight crimp plug for Mini RG59 black cable
BNC-C-MULTI	100 BNC plugs RG59 in zip bag with spare pins and ferrules
BNC-C-RG11	BNC straight crimp for RG11

Anixter Number	Cable Type
CRIMPTOOL-1	RG59, CT100, RG59, Mini RG59
CRIMPTOOL-2	CT125
CRIMPTOOL-3	RG11 & RG213
SRB-RG59-02	Strain relief boots for RG59 connectors PVC black