

A1/A2 Brass Gland with Outer Seal



- To BS6121 : Part 1.
- Suitable for unarmoured, plastic or rubber sheathed cables.
- Suitable for most indoor and outdoor applications.
- Seal rated to IP66.

Cable & Gland Details

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)	
			Overall Diameter	Minimum
E1AW-A1/A2-16/20C	CMP	16/20	3.1	8.7
E1AW-A1/A2-20SS	Prysmian	20SS	3.5	8.5
E1AW-A1/A2-20SC	CMP	20S	6.1	11.7
E1AW-A1/A2-20S	Prysmian	20S	8.0	11.6
E1AW-A1/A2-20C	CMP	20	6.5	14.0
E1AW-A1/A2-20	Prysmian	20	11.0	13.5
E1AW-A1/A2-25C	CMP	25	11.1	20.0
E1AW-A1/A2-25	Prysmian	25	13.0	19.5
E1AW-A1/A2-32C	CMP	32	17.0	26.3
E1AW-A1/A2-32	Prysmian	32	19.0	25.5
E1AW-A1/A2-40C	CMP	40	23.5	32.2
E1AW-A1/A2-40	Prysmian	40	25.0	32.0
E1AW-A1/A2-50SC	CMP	50S	31.0	38.2
E1AW-A1/A2-50S	Prysmian	50S	31.5	37.0
E1AW-A1/A2-50C	CMP	50	35.6	44.1
E1AW-A1/A2-50	Prysmian	50	36.5	43.0
E1AW-A1/A2-63SC	CMP	63S	41.5	50.0
E1AW-A1/A2-63S	Prysmian	63S	42.5	50.0

Glands are supplied in kit form, complete with locknuts and shrouds.

Up to size 25:- 2 per kit.

Size 32 and above:- 1 per kit, with exception of CMP size 32 which contains 2 per kit.