

CX Brass Gland with Outer Seal



- To BS6121 : Part 1.
- Suitable for wire braid armoured, plastic or rubber sheathed cables.
- Outer seal grips sheath of cable.
- Seal rated to IP66.

- Weatherproof and water proof.
- Seal rated to IP66.
- Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface.

Cable & Gland Details

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1AH-CX-16/20C	CMP	16/20	-	8.7	6.1	11.5
E1AH-CX-20SS	Prysmian	20SS	-	8.6	8.0	13.2
E1AH-CX-20SC	CMP	20S	-	11.7	9.5	15.9
E1AH-CX-20S	Prysmian	20S	-	11.6	8.0	15.8
E1AH-CX-20C	CMP	20	-	14.0	12.5	20.9
E1AH-CX-20	Prysmian	20	-	13.9	12.9	20.8
E1AH-CX-25C	CMP	25	-	20.0	18.2	26.2
E1AH-CX-25	Prysmian	25	-	19.9	17.0	27.2
E1AH-CX-32C	CMP	32	-	26.3	23.7	33.9
E1AH-CX-32	Prysmian	32	-	26.2	23.5	33.5
E1AH-CX-40C	CMP	40	-	32.2	27.9	40.4
E1AH-CX-40	Prysmian	40	-	32.1	29.0	39.9

Glands are supplied in kit form, complete with locknuts, earhtags and shrouds.

Up to size 25:- 2 per kit.

Size 32 and above:- 1 per kit, with exception of CMP size 32 which contains 2 per kit.