

## CW Brass Gland with Outer Seal



- To BS6121 : Part 1.
- Suitable for wire braid armoured, plastic or rubber sheathed cables.
- Outer seal grips sheath of cable.
- Seal rated to IP66.

- Weatherproof and water proof.
- Seal rated to IP66.
- Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface.

Brass glands are provided with steel locknuts and aluminium glands are provided with aluminium locknuts. For more corrosive environments brass locknuts may be supplied.

Glands are supplied in kit form, complete with locknuts, earthtags and shrouds.

Prysmian

Up to size 25:- 2 per kit  
Size 32 and above:- 1 per kit

CMP

Up to size 32:- 2 per kit  
Size 40 and above:- 1 per kit

# CW (Brass or Aluminium) Gland with Outer Seal

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1AG-CW-16/20	CMP	16/20	-	8.7	6.1	11.5
E1AG-CW-20SSC	Prysmian	20SS	-	8.6	8.0	13.2
E1AG-CW-20S	CMP	20S	-	11.7	9.5	15.9
E1AG-CW-20SC	Prysmian	20S	-	11.6	8.0	15.8
E1AG-CW-20	CMP	20	-	14.0	12.5	20.9
E1AG-CW-20C	Prysmian	20	-	13.9	11.7	20.8
E1AG-CW-25	CMP	25	-	20.0	18.2	26.2
E1AG-CW-25C	Prysmian	25	-	19.9	17.0	27.2
E1AG-CW-32	CMP	32	-	26.3	23.7	33.9
E1AG-CW-32C	Prysmian	32	-	26.2	23.5	33.5
E1AG-CW-40	CMP	40	-	32.2	27.9	40.4
E1AG-CW-40C	Prysmian	40	-	32.1	29.0	39.9
E1AG-CW-50S	CMP	50S	-	38.2	35.2	46.7
E1AG-CW-50	CMP	50	-	44.1	40.4	53.1
E1AG-CW-50C	Prysmian	50	-	44.0	39.5	52.6
E1AG-CW-63S	CMP	63S	-	50.0	45.6	59.4
E1AG-CW-63	CMP	63	-	56.0	54.6	65.9
E1AG-CW-63C	Prysmian	63	-	55.9	51.3	65.3
E1AG-CW-75S	CMP	75S	-	62.0	59.0	72.1
E1AG-CW-75	CMP	75	-	68.0	66.7	78.5
E1AG-CW-75C	Prysmian	75	-	67.9	62.5	78.0
<b>Aluminium CW glands for aluminium wire armoured cable</b>						
E1DN-CW-25C	CMP	25	-	20.0	18.2	26.2
E1DN-CW-32C	CMP	32	-	26.3	23.7	33.9
E1DN-CW-40C	CMP	40	-	32.2	27.9	40.4
E1DN-CW-50SC	CMP	50S	-	38.2	35.2	46.7
E1DN-CW-50C	CMP	50	-	44.1	40.4	53.1