

E1W Brass Gland with Inner and Outer Seals



- To BS6121 : Part 1.
- Suitable for single wire armoured, plastic or rubber sheathed cables.
- Outer seal grips sheath of cable.
- Inner seal grips bedded layer of cable.
- Weatherproof and waterproof.
- Inner and outer seal rated to IP66.
- Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface.

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1BA-E1W-16/20C	CMP	16/20	3.1	8.7	6.1	11.5
E1BA-E1W-20SS	Prysmian	20SS	6.3	8.6	8.0	13.2
E1BA-E1W-20SC	CMP	20S	6.1	11.7	9.5	15.9
E1BA-E1W-20S	Prysmian	20S	8.7	11.6	8.0	15.8
E1BA-E1W-20C	CMP	20	6.5	14.0	12.5	20.9
E1BA-E1W-20	Prysmian	20	11.7	13.9	11.7	20.8
E1BA-E1W-25C	CMP	25	11.1	20.0	18.2	26.2
E1BA-E1W-25	Prysmian	25	13.0	19.9	17.0	27.2
E1BA-E1W-32C	CMP	32	17.0	26.3	23.7	33.9
E1BA-E1W-32	Prysmian	32	20.0	26.2	23.5	33.5
E1BA-E1W-40C	CMP	40	22.0	32.2	27.9	40.4
E1BA-E1W-40	Prysmian	40	26.3	32.1	29.0	39.9
E1BA-E1W-50SC	CMP	50S	29.5	38.2	35.2	46.7
E1BA-E1W-50S	Prysmian	50S	32.2	38.1	38.0	46.2
E1BA-E1W-50C	CMP	50	35.6	44.1	40.4	53.1
E1BA-E1W-50	Prysmian	50	38.2	44.0	39.5	52.6
E1BA-E1W-63SC	CMP	63S	40.1	50.0	45.6	59.4
E1BA-E1W-63C	CMP	63	47.2	56.0	54.6	65.9
E1BA-E1W-63	Prysmian	63	50.1	55.9	51.3	65.3
E1BA-E1W-75SC	CMP	75S	52.8	62.0	59.0	72.1
E1BA-E1W-75C	CMP	75	59.1	68.0	66.7	78.5
E1BA-E1W-75	Prysmian	75	62.0	67.9	62.5	78.0

Glands are supplied in kit form, complete with locknuts, earhtags and shrouds.

Prysmian

Up to size 25:- 2 per kit
Size 32 and above:- 1 per kit

CMP

Up to size 32:- 2 per kit
Size 40 and above:- 1 per kit