

1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19

Accessories

CW Brass Gland with Outer LSF Seal

- To BS6121 : Part 1.
- Suitable for wire braid armoured, plastic or rubber sheathed cables.
- Outer LSF seal grips sheath of cable.
- Seal rated to IP66.
- Weatherproof and water proof.
- Seal rated to IP66.
- Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface.

Glands are supplied in kit form, complete with locknuts, earthtags and shrouds.

Prysmian - Up to size 25:- 2 per kit
 Size 32 and above:- 1 per kit

CMP - Up to size 32:- 2 per kit
 Size 40 and above:- 1 per kit

CW Gland with Outer LSF Seal

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1AG-CW-20SSLSF	Prysmian	20SS	-	8.6	8.0	13.2
E1AG-CW-20SCLSF	CMP	20S	-	11.7	9.5	15.9
E1AG-CW-20LSF	Prysmian	20S	-	11.6	8.0	15.8
E1AG-CW-20CLSF	CMP	20	-	14.0	12.5	20.9
E1AG-CW-20LSF	Prysmian	20	-	13.9	11.7	20.8
E1AG-CW-25SCLSF	CMP	25	-	20.0	18.2	26.2
E1AG-CW-25LSF	Prysmian	25	-	19.9	17.0	27.2
E1AG-CW-32SCLSF	CMP	32	-	26.3	23.7	33.9
E1AG-CW-32LSF	Prysmian	32	-	26.2	23.5	33.5
E1AG-CW-40SCLSF	CMP	40	-	32.2	27.9	40.4
E1AG-CW-40LSF	Prysmian	40	-	32.1	29.0	39.9
E1AG-CW-50SCLSF	CMP	50S	-	38.2	35.2	46.7
E1AG-CW-50LSF	Prysmian	50S	-	38.1	38.0	46.2
E1AG-CW-50SCLSF	CMP	50	-	44.1	40.4	53.1
E1AG-CW-50LSF	Prysmian	50	-	44.0	39.5	52.6
E1AG-CW-63SCLSF	CMP	63S	-	50.0	45.6	59.4
E1AG-CW-63SCLSF	CMP	63	-	56.0	54.6	65.9
E1AG-CW-63LSF	Prysmian	63	-	55.9	51.3	65.3
E1AG-CW-75SCLSF	CMP	75S	-	62.0	59.0	72.1
E1AG-CW-75SCLSF	CMP	75	-	68.0	66.7	78.5
E1AG-CW-75LSF	Prysmian	75	-	67.9	62.5	78.0