

A2F & A2EX Flameproof & Increased Safety Brass Gland with Outer Seal



- Suitable for unarmoured, plastic or rubber sheathed cables.
- Suitable for most indoor and outdoor applications
- Seal rated to IP66.
- Complies with IIA, IIB and IIC hazardous atmospheres (EN60079).
- Zone 1 and Zone 2 applications.
- For use with flameproof and increased safety equipment (E.Exd and E.Exe).
- ATEX Certified.

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)	
			Overall	
			Minimum	Maximum
E1AT-A2F-16/20C	CMP	16/20	3.2	8.7
E1AT-A2EX-20SS	Prysmian	20SS	3.5	8.5
E1AT-A2F-20SC	CMP	20S	6.1	11.7
E1AT-A2EX-20S	Prysmian	20S	8.0	11.5
E1AT-A2F-20C	CMP	20	6.5	14.0
E1AT-A2EX-20	Prysmian	20	8.0	16.0
E1AT-A2F-25C	CMP	25	11.1	20.0
E1AT-A2EX-25	Prysmian	25	11.5	21.0
E1AT-A2F-32C	CMP	32	17.0	26.3
E1AT-A2EX-32	Prysmian	32	18.5	27.5
E1AT-A2F-40C	CMP	40	23.5	32.2
E1AT-A2EX-40	Prysmian	40	24.0	34.0
E1AT-A2F-50SC	CMP	50S	31.0	38.2
E1AT-A2F-50C	CMP	50	35.6	44.1
E1AT-A2EX-50	Prysmian	50	31.0	41.0
E1AT-A2F-63SC	CMP	63S	41.5	50.0
E1AT-A2F-63C	CMP	63	47.2	56.0
E1AT-A2EX-63	Prysmian	63	40.0	52.5

Glands are supplied in kit form, complete with locknuts and shrouds.

Up to size 25:- 2 per kit

Size 32 and above:- 1 per kit, with exception of CMP size 32 which contains 2 per kit.