

Telcleats – Black Polythene & Grey LSF



- Range taking and self adjusting.
- Just 8 sizes cover from 10mm to 51mm diameter.
- Ultraviolet and weather resistant.
- Low cost.
- Versatile.
- One piece.
- Single fixing.
- LSF cleats are low smoke and fume emission and zero halogen.
- Coloured grey to distinguish from black coloured Telcleat.
- Meets requirements of BS6853 and LUL specification 1-085 (formerly 2-01001-2 and E1042) with regards to temperature index, smoke emission and toxicity ratings.

Cleat Details

| Anixter Number | Cable Dimensions Accommodated | |
|------------------------|-------------------------------|--------------|
| | Minimum (mm) | Maximum (mm) |
| Black Polythene | | |
| E1D-A01 | 10.5 | 14.5 |
| E1D-A02 | 12.2 | 16.7 |
| E1D-A03 | 14.6 | 19.8 |
| E1D-A04 | 17.7 | 24.0 |
| E1D-A05 | 21.7 | 28.5 |
| E1D-A06 | 26.2 | 34.2 |
| E1D-A07 | 31.9 | 41.6 |
| E1D-A08 | 39.3 | 51.1 |
| Grey LSF | | |
| E1D-A01LSF | 10.5 | 14.5 |
| E1D-A02LSF | 12.2 | 16.7 |
| E1D-A03LSF | 14.6 | 19.8 |
| E1D-A04LSF | 17.7 | 24.0 |
| E1D-A05LSF | 21.7 | 28.5 |
| E1D-A06LSF | 26.2 | 34.2 |
| E1D-A07LSF | 31.9 | 41.6 |
| E1D-A08LSF | 39.3 | 51.1 |

Telcleats – Black Polythene & Grey LSF

Cleat Selection Chart

| Cond Size sqmm | Core 1 | Core 2 | Core 3 | Core 4 | Core 5 | Core 7 | Core 12 | Core 19 | Core 27 | Core 37 |
|----------------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 1.5 | - | C5 | C5 | C6 | C6 | C6 | C8 | C9 | C10 | C12 |
| 2.5 | - | C6 | C6 | C6 | C7 | C7 | C9 | C10 | C12 | C14 |
| 4 | - | C7 | C7 | C7 | C8 | C8 | C11 | - | - | - |
| 6 | - | C7 | C8 | C8 | C8 | C9 | C12 | - | - | - |
| 10 | - | C8 | C9 | C9 | C10 | C11 | - | - | - | - |
| 16 | - | C9 | C10 | C11 | C11 | C12 | - | - | - | - |
| 25 | - | C12 | C12 | C12 | C14 | C16 | - | - | - | - |
| 35 | - | C12 | C12 | C14 | C14 | - | - | - | - | - |
| 50 | C8 | C11 | C12 | C14 | C16 | - | - | - | - | - |
| 70 | C9 | C12 | C14 | C16 | C18 | - | - | - | - | - |
| 95 | C10 | C14 | C16 | C18 | C20 | - | - | - | - | - |
| 120 | C11 | C16 | C19 | C20 | MT9 | - | - | - | - | - |
| 150 | C12 | C18 | C20 | MT9 | - | - | - | - | - | - |
| 185 | C14 | C20 | MT9 | MT10 | - | - | - | - | - | - |
| 240 | C14 | MT9 | MT10 | MT11 | - | - | - | - | - | - |
| 300 | C16 | MT9 | MT10 | MT12 | - | - | - | - | - | - |
| 400 | C18 | MT10 | MT11 | MT14 | - | - | - | - | - | - |

Please note that the above chart is a guide, and cable OD should be checked prior to cleat selection.