

BW Brass Gland



- To BS6121: Part 1.
- Suitable for single wire armoured, plastic or rubber sheathed cables.
- For use in dry indoor situations.
- Low-cost two-part design.
- IP54.
- Shroud may be used for additional ingress protection.

Brass glands are provided with steel locknuts. For more corrosive environments brass locknuts may be supplied.

Anixter Number	Gland Manufacturer	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1AJ-BW-20SC	Prysmian	20S	-	11.6	-	15.8
E1AJ-BW-20S	CMP	20S	-	11.7	-	16.1
E1AJ-BW-20C	Prysmian	20	-	13.9	-	20.8
E1AJ-BW-20	CMP	20	-	14.0	-	21.1
E1AJ-BW-25C	Prysmian	25	-	19.9	-	27.2
E1AJ-BW-25	CMP	25	-	20.0	-	27.4
E1AJ-BW-32C	Prysmian	32	-	26.2	-	33.5
E1AJ-BW-32	CMP	32	-	26.3	-	34.4
E1AJ-BW-40C	Prysmian	40	-	32.1	-	39.9
E1AJ-BW-40	CMP	40	-	32.2	-	42.4
E1AJ-BW-50S	CMP	50S	-	38.2	-	50.1
E1AJ-BW-50C	Prysmian	50	-	44.0	-	52.6
E1AJ-BW-50	CMP	50	-	44.1	-	55.7
E1AJ-BW-63S	CMP	63S	-	50.0	-	62.4
E1AJ-BW-63C	Prysmian	63	-	55.9	-	65.3
E1AJ-BW-63	CMP	63	-	56.0	-	68.2
E1AJ-BW-75S	CMP	75S	-	62.0	-	76.8
E1AJ-BW-75C	Prysmian	75	-	67.9	-	78.0
E1AJ-BW-75	CMP	75	-	75.0	-	82.9

Glands are supplied in kit form, complete with locknuts, earthtags and shrouds.

Prysmian

Up to size 25:- 2 per kit

Size 32 and above:- 1 per kit

CMP

Up to size 32:- 2 per kit

Size 40 and above:- 1 per kit