

# Specialty Wrenches

## Can Wrench

- Two tools in one; saves space in your pouch.
- One end opens telephone box fasteners, the other end tightens nuts on binding-post terminals.
- The 7/16" socket has a black finish and the 3/8" socket has a silver finish.
- Sockets are 1-1/4" (32 mm) deep to fit over long binding posts and are thin-walled for easy access into tight areas.
- Socket ends are color-coded for quick identification of socket sizes.



68005

- Hex-socket design enables using a wrench to obtain extra torque.
- High-impact, break-resistant handle for long and dependable service.
- Sockets are heat-treated, alloy steel.

Cat. No.	Description	Length	Handle Dia.	Weight (lbs.)
68005	3/8" and 7/16" hex nut	7" (178 mm)	1" (25 mm)	.35

**⚠WARNING:** NOT insulated. Will NOT protect against electrical shock.

## Bell System Type

- Similar to standard lineman's wrench, but with end openings sized to NEMA hardware specifications.
- Silver painted finish.



3146B

Cat. No.	Description	Length	Weight (lbs.)
3146B	Large end has 1-1/16" and 1-3/16" openings. Small end has 11/16" and 7/8" openings.	13" (330 mm)	1.76

## Lineman's Wrenches

- Forged from special bar steel and heat-treated for long life.
- Each end has two different size openings.
- Hole is provided at larger end for turning-in standard pole steps.
- Wrench is suited for use on heavy three-bolt guy clamps on which clearance is limited.



3146

- Dark blue painted finish (small end is painted silver on Cat. No. 3146A).

Cat. No.	Description	Length	Weight (lbs.)
3146	For 5/8" hardware. Large end has 29/32" and 1-3/32" openings. Small end has 5/8" and 13/16" openings.	13" (330 mm)	1.85
3146A	For 3/4" hardware. Large end has 1-1/16" and 1-5/16" openings. Small end has 5/8" and 7/8" openings.	13" (330 mm)	1.70

## 3-in-1 Impact Socket

- Includes 3/4" (also works on 13/16"), 1" and 1-1/8" square sizes.
- Fine tuned ball detent provides improved retention, minimizing drops.
- 7/16" hex quick-change adapter included.
- 13/16" diameter, 6" long hollow shaft allows use on long threaded bolts.

NEW!



NRHD

NRHDA  
Replacement Adapter

Cat. No.	Description	Length	Weight (lbs.)
NRHD	3-in-1 Impact Socket	7-3/4" (197 mm)	2.0

### Replacement Parts

NRHDA Impact Socket Adapter



NRHDA

## Lineman's Ratcheting Wrenches

- Bolt-through design allows bolts to pass through the socket.
- 3/4" and 1" x 1-1/8" combination square socket for most common utility hardware.
- Bright yellow socket for easy visibility.
- Works on most common utility pole hardware, such as lag bolts, "C" clamps and suspension bolts.
- KT155T and KT155HD also offer two popular wrench sizes: 9/16" and 3/4".
- Heavy duty design (KT155HD).



KT151T



KT155HD

Cat. No.	Description	Length	Weight (lbs.)
KT155HD	Ratcheting Lineman's Wrench - Heavy Duty	12" (305 mm)	2.10
KT151T	Ratcheting Lineman's Wrench	13" (330 mm)	2.12
KT155T	5-in-1 Lineman's Wrench	9-3/8" (238 mm)	1.42



KT155T

All dimensions are in inches and (millimeters).

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Do NOT push or hammer wrench.

**⚠WARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

**⚠WARNING:** Do NOT extend handle length.