

Tool Kits

Utility Insulated 13-Piece Tool Kit

- An assortment of 13 professional, insulated tools.
- The custom case includes two pallets with custom-fitted pockets for each tool, piano-hinged case cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items.
- Case's inside dimensions are: 17-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm).
- Overall case dimensions are: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm).
- Replacement case available Cat. No. 33535.



Cat. No.	Kit Contains	Weight
33525		20.05 lbs. (9 kg)



33525

Cat. No.	Description
D2000-9NE-INS	insulated side-cutting pliers
D2000-28-INS	insulated diagonal-cutting pliers
D2000-48-INS	insulated diagonal-cutting pliers – angled head
D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")

Cat. No.	Description
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535	extra-sturdy, bright-yellow case

Utility Insulated 13-Piece Tool Kit

- The light, compact, soft roll-up carry case provides protective storage with custom-fitted pockets for each tool.
- Kit includes a padded, adjustable shoulder strap.
- Overall carrying case dimensions:
Opened 24.5" x 24.5" (622.3 mm x 622.3 mm).
Closed 24.5" x 5.5" (622.3 mm x 139.7 mm).
- Replacement Roll-Up case available Cat. No. 33535SC.



Cat. No.	Kit Contains	Weight
33525SC		9.75 lbs. (4.4 kg)




33525SC

Cat. No.	Description
D2000-9NE-INS	insulated side-cutting pliers
D2000-28-INS	insulated diagonal-cutting pliers
D2000-48-INS	insulated diagonal-cutting pliers – angled head
D203-8-INS	insulated heavy-duty long-nose pliers – side-cutting
602-4-INS	insulated cabinet-tip – round-shank screwdriver (1/4" x 4")
602-7-INS	insulated cabinet-tip – round-shank screwdriver (5/16" x 7")
602-8-INS	insulated cabinet-tip – round-shank screwdriver (3/8" x 8")
633-4-INS	insulated Phillips-tip – round-shank screwdriver (#1 x 4")

Cat. No.	Description
603-4-INS	insulated Phillips-tip – round-shank screwdriver (#2 x 4")
633-7-INS	insulated Phillips-tip – round-shank screwdriver (#3 x 7")
63050-INS	insulated high-leverage cable cutter
D502-10-INS	insulated pump pliers
1571-INS	insulated lineman's skinning knife
33535SC	roll-up soft case with shoulder strap

All dimensions are in inches and (millimeters).

▲WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



▲WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

▲WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

▲WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

▲WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

