

JOURNEYMAN

Cat. No.	Description
605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
631	7-piece cushion-grip nut driver set (3/16", 1/4", 5/16", 11/32", 3/8", 7/16", 1/2")
650	cushion-grip scratch awl
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Drive®
93125	25' x 1" tape measure with magnetic tip
931-9RE	torpedo level - magnetic
J1005	Journeyman™ crimping/cutting tool – non-insulated and insulated connectors
K1412	Klein-Kurve® dual NM cable stripper/cutter
J2000-9NETP	Journeyman™ high-leverage side-cutting pliers – fish tape pulling
J2000-48	Journeyman™ high-leverage diagonal-cutting pliers – angled head
5003-18	18" 10-pocket canvas tool bag with leather bottom
5139	canvas zipper bag
11055	Klein-Kurve® wire stripper/cutter – 10-18 AWG solid & 12-20 AWG stranded
44133	Klein-Kurve® heavy-duty utility knife – quick change retractable blade
46037	cable-splicer's kit
56003	Steel Fish Tape - 125' L x 1/8" W
58889	padded adjustable shoulder strap
60053	standard protective eyewear
J63050	Journeyman™ high-leverage cable cutter
85191	conduit-fitting and reaming screwdriver

334