

Tool Sets

18-Piece Journeyman™ Tool Set

JOURNEYMAN



80118

Cat. No.	Set Contains	Weight (lbs.)
80118		11.6

Cat. No.	Description
J203-8N	Journeyman™ heavy-duty long-nose pliers – side-cutting & stripping
J502-10	10" Journeyman™ pump pliers with 1-3/4" (44 mm) jaw capacity
D507-10	10" adjustable wrench – extra capacity
603-3	No. 1 Phillips cushion-grip screwdriver – 3" (76 mm) round-shank
603-4B	wire bending No. 2 Phillips cushion-grip screwdriver – 4" (102 mm) round-shank
605-4	1/4" cabinet-tip cushion-grip screwdriver – 4" (102 mm) heavy-duty round-shank
605-6	1/4" cabinet-tip cushion-grip screwdriver – 6" (152 mm) heavy-duty round-shank
630-1/4	1/4" cushion-grip nut driver – 3" (76 mm) shank
630-5/16	5/16" cushion-grip nut driver – 3" (76 mm) shank
662	No. 2 square-recess tip cushion-grip screwdriver – 4" (102 mm) round-shank

Cat. No.	Description
670-6	3/16" cabinet-tip cushion-grip screwdriver – Rapi-Drive®
93125	25' x 1" tape measure with magnetic tip
J2000-9NETP	Journeyman™ high-leverage side-cutting pliers – fish tape pulling
J2000-48	Journeyman™ high-leverage diagonal-cutting pliers - angled head
5165	10-pocket leather tool pouch
5705	Powerline™ web work belt
11055	Klein-Kurve® wire stripper/cutter – 10-18 AWG solid & 12-20 AWG stranded
60053	standard protective eyewear

All dimensions are in inches and (millimeters) unless otherwise specified.

▲WARNING: The tool belt provided in this kit is NOT an occupational protective belt.

▲WARNING: NOT insulated. Do NOT use these tools on or near live electrical circuits.

▲WARNING: Do NOT use screwdrivers to pry or chisel.

▲WARNING: Always wear approved eye protection.

▲WARNING: Do NOT open the tape measure case. Spring motor is under tension, and opening may cause injury.

