



[Home](#) » [Catalog](#) » [Insulated Tools](#) » [Insulated Screwdrivers](#) » [Insulated Cabinet-Tip - Round-Shank](#)

Insulated 3/8" Cabinet-Tip 8" Round-Shank Screwdriver



Cat. No. 602-8-INS

Product Features

1000V Rated for safety.

Durable, two-layer, molded insulation to meet or exceed all ASTM and IEC standards for insulated tools.

Custom US-made tool steel.

Cushion-Grip handle for superior torque and comfort.

Made in the USA.

This sku replaces 602-10-INS.

BUY NOW

FIND RETAILER



MADE IN



USA

Specifications

Downloads

Warnings

Overall Length: 13-3/8"

Shank Tip Width: 3/8"

Shank Length: 8"

Weight (lbs.): .52

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)



© 2013 Klein Tools, Inc. • All Rights Reserved • 450 Bond Street • Lincolnshire, IL 60069 • USA • phone: 800-553-4676 • fax: 800-553-4876

[Privacy Policy](#) | [Terms & Conditions](#)