





For Professionals... Since 1857®

WHERE TO BUY

[Home](#) » [Catalog](#) » [Insulated Tools](#) » [Insulated Screwdrivers](#) » [Insulated Phillips-Tip - Round-Shank](#)

Insulated #2 Phillips-Tip - 4" Round-Shank Screwdriver



Cat. No. 603-4-INS

Product Features

*1000V rated for safety
Durable, two-layer, molded insulation to meet or exceed all ASTM and IEC standards for insulated tools.
Cushion-Grip handles for greater torque and comfort.
Custom US-made steel.
Made in the USA.*

BUY NOW

FIND RETAILER



Specifications

Downloads

Warnings

Overall Length: 8-5/16"

Shank Length: 4"

Weight (lbs.): .21

Point Size: #2

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)



© 2013 Klein Tools, Inc. • All Rights Reserved • 450 Bond Street • Lincolnshire, IL 60069 • USA • phone: 800-553-4676 • fax: 800-553-4876
[Privacy Policy](#) | [Terms & Conditions](#)