



[Home](#) » [Catalog](#) » [Insulated Tools](#) » [Insulated Nut Drivers](#) » [Insulated 6" Hollow-Shaft Nut Drivers](#)

Insulated Cushion-Grip, 11/32" Hollow-Shaft Nut Driver 6" Shank



Cat. No. 646-11/32-INS

Product Features

Individually tested to exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and clearly marked with the official 1000-volt rating symbol.

Two layers of insulation provide protection against electric shock. Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool.

A flame retardant, impact-resistant, bright orange outer coating.

Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications.

Patented Tip-Ident quickly identifies nut driver size.

Cushion-Grip handles for greater torque and comfort.

BUY NOW

FIND RETAILER



Specifications

Downloads

Warnings

Shank Length: 6"

Weight (lbs.): .19

Hex Size: 11/32"

Overall Length: 9-3/4"

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)



© 2013 Klein Tools, Inc. • All Rights Reserved • 450 Bond Street • Lincolnshire, IL 60069 • USA • phone: 800-553-4676 • fax: 800-553-4876

[Privacy Policy](#) | [Terms & Conditions](#)